

Garant

**Side lock arbor Form ADB with cooling channel bores, SK 40 A = 160,
Clamping range \varnothing D1: 8mm**



Order data

Order number	300276 8
GTIN	4045197829849
Item class	31A

Description

Version:

GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

With coolant supply holes that can be plugged.

With Balluff/RFID chip bore.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	160 mm
Spare clamping screw No. 30 9900	8
Clamping \varnothing D ₁	8 mm
External \varnothing D	28 mm
Adapter	SK 40 A = 160
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull studsealed suitable for steep tapers 40	308635 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
	308820 40

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872)
suitable for ISO taper size 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers
40

308630 40

Pull stud Mazak, form A suitable for steep tapers 40M

308670 40M

Pull stud Form A suitable for steep tapers 40

308600 40

Pull stud 45° sealed suitable for steep tapers 40

308760 40

Pull stud 60° sealed suitable for steep tapers 40

308785 40

Pull stud Hurco 90° with fit sealed suitable for steep tapers
40

308806 40

Spare clamping screw for chucks with clamping \varnothing D1 8
mm

309900 8