



Jaw 64 mm, for T-Rex fixed, for type: 125



Order data

Order number	361220 125
GTIN	4250364400732
Item class	34A

Description

Application:

For clamping small to medium workpieces. Blanks can be clamped using 2 adjustable gripp inserts. Smooth clamping faces for clamping pre-machined workpieces.

Suitable for :

Fixed jaws for T-Rex No. 361202.

Jaw width b: 116 mm

Width b₁: 64 mm

Jaw height h: 45 mm

Height h₂: 14 mm

Jaw length l: 67 mm

n₁: 37 mm

Technical description

Jaw height h	45 mm
suitable for colour code	T-Rex
n ₁	37 mm
Jaw length l	67 mm
Jaw width b	116 mm
Width b ₁	64 mm

Clamping range S2	66 – 138 mm
for type	125
Clamping range S3	131 – 209 mm
Clamping range S1	21 – 68 mm
Height h ₂	14 mm
Type of product	Vice jaws