



## Hook toggle clamp vertical, Type: 4



### Order data

Order number	376820 4
GTIN	4020772008666
Item class	35A

### Description

#### Version:

- **Quick-action clamp with toggle action.**
- **Self-locking mechanism prevents inadvertent opening.**
- **Rivet of stainless steel.**
- **Handle made of oil-resistant plastic.**
- **Galvanised clamps.**
- **Clamping hook adjustable using thread.**
- **Bearing bushes case-hardened.**
- **Bearings greased.**
- **Hardened hook.**

Complete with catch.

#### Application:

For closing containers.

#### Note:

- **More compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

### Technical description

Clamping force P (traction)	7000 N
Adjustment travel of clamping hook c	9 - 47 mm
Hole spacing e	32 mm
Hole spacing f	35 - 46 mm
Bore $\varnothing$ d	8.5 mm
Clamping height h	26 mm
Overall height H	94.5 mm
Overall length L	151 mm
Type	6848VJ
Type of product	Hook toggle clamp