



Quick-action table clamp, Type: BS2N



Order data

Order number	377065 BS2N
GTIN	4008158018133
Item class	37B

Description

Version:

Steplessly variable, fixed or pivoted. Type BS – the clamping action is released by tightening the clamping handle further then pressing the release lever (clamp then releases easily). Type GRS – the spindle is located away from the head, allowing free access to the work area.

Application:

For use on machine tables for fast and reliable clamping and releasing when manufacturing individual parts.

Optional extras:

Socket-head screw to DIN 912, T-nuts No. 375315; 375320; 375325 to DIN 508.

Technical description

Throat	100 mm
maximum clamping force at 50mm clamping height	3.5 kN
Clamping height h	200 mm
Height H	260 mm

Attachment hole Ø	10.5 mm
Type of product	Quick clamp

Accessories

T-nut long T-slot nominal size / thread 12/M10 mm	375325 12/M10
T-nutBlank T-slot nominal size 14 mm	375320 14
T-nutBlank T-slot nominal size 20 mm	375320 20
T-nut long T-slot nominal size / thread 14/M12 mm	375325 14/M12
T-nutBlank T-slot nominal size 10 mm	375320 10
T-nut long T-slot nominal size / thread 22/M20 mm	375325 22/M20
T-nutBlank T-slot nominal size 18 mm	375320 18
T-nut long T-slot nominal size / thread 8/M6 mm	375325 8/M6
T-nut long T-slot nominal size / thread 18/M16 mm	375325 18/M16
T-nutwith threaded shank T-slot nominal size 24 mm	375315 24
T-nutBlank T-slot nominal size 24 mm	375320 24
T-nutwith threaded shank T-slot nominal size 14 mm	375315 14
T-nutBlank T-slot nominal size 12 mm	375320 12
T-nutwith threaded shank T-slot nominal size 10 mm	375315 10
T-nutBlank T-slot nominal size 6 mm	375320 6
T-nut long T-slot nominal size / thread 28/M24 mm	375325 28/M24
T-nutwith threaded shank T-slot nominal size 28 mm	375315 28
T-nutwith threaded shank T-slot nominal size 6 mm	375315 6
T-nutwith threaded shank T-slot nominal size 36 mm	375315 36
T-nutwith threaded shank T-slot nominal size 16 mm	375315 16
T-nut long T-slot nominal size / thread 16/M14 mm	375325 16/M14
T-nutwith threaded shank T-slot nominal size 32 mm	375315 32
T-nutBlank T-slot nominal size 16 mm	375320 16
T-nutwith threaded shank T-slot nominal size 18 mm	375315 18

T-nut long T-slot nominal size / thread 20/M18 mm	375325 20/M18
T-nutwith threaded shank T-slot nominal size 8 mm	375315 8
T-nutwith threaded shank T-slot nominal size 20 mm	375315 20
T-nutBlank T-slot nominal size 8 mm	375320 8
T-nutwith threaded shank T-slot nominal size 22 mm	375315 22
T-nut long T-slot nominal size / thread 10/M8 mm	375325 10/M8
T-nutwith threaded shank T-slot nominal size 12 mm	375315 12
T-nutBlank T-slot nominal size 22 mm	375320 22
T-nutBlank T-slot nominal size 28 mm	375320 28