



Hook toggle clamp heavy-duty, Type: 5



Order data

Order number	376840 5
GTIN	4020772093853
Item class	35A

Description

Version:

Base, lever arm, and catch of cast steel, pin of hardened steel. For high retaining force.

Technical description

Hole spacing f	57 mm
Adjustment travel of clamping hook c	28 - 93 mm
Bore \varnothing d	10.5 mm
Clamping force P (traction)	27000 N
Hole spacing e	57 mm
Clamping height h	32 mm
Overall height H	146 mm
Overall length L	250 mm
Type	6849PH
Type of product	Hook toggle clamp

