



Jaw 20 mm, for T-Rex fixed, for type: 125



Order data

Order number	361225 125
GTIN	4250364400756
Item class	34A

Description

Application:

Clamping faces coated for high friction values, increased gripping power by a factor of at least 2 (typical hardness 80 HRC).

Suitable for :

Fixed jaws for T-Rex No. 361202.

Jaw width b: 116 mm

Width b₁: 20 mm

c: 14 mm

c₁: 20 mm

Jaw height h: 50 mm

Height h₁: 45 mm

Technical description

Height h ₂	14 mm
Jaw height h	50 mm
Clamping range S1	9 – 75 mm
l ₁	4 mm
Width b ₁	20 mm
c	14 mm

Height h_1	45 mm
Jaw length l	62 mm
c_1	20 mm
Jaw width b	116 mm
for type	125
suitable for colour code	T-Rex
Type of product	Vice jaws