



Quick-action table clamp, Type: BS5N



Order data

| | |
|--------------|---------------|
| Order number | 377065 BS5N |
| GTIN | 4008158018164 |
| Item class | 37B |

Description

Version:

Steplessly variable, fixed or pivoted. Type BS – the clamping action is released by tightening the clamping handle further then pressing the release lever (clamp then releases easily). Type GRS – the spindle is located away from the head, allowing free access to the work area.

Application:

For use on machine tables for fast and reliable clamping and releasing when manufacturing individual parts.

Optional extras:

Socket-head screw to DIN 912, T-nuts No. 375315; 375320; 375325 to DIN 508.

Technical description

| | |
|--|--------|
| maximum clamping force at 50mm clamping height | 10 kN |
| Throat | 140 mm |
| Clamping height h | 240 mm |
| Height H | 320 mm |

| | |
|-------------------|-------------|
| Attachment hole Ø | 16.5 mm |
| Type of product | Quick clamp |

Accessories

| | |
|--|---------------|
| T-nutwith threaded shank T-slot nominal size 10 mm | 375315 10 |
| T-nutBlank T-slot nominal size 24 mm | 375320 24 |
| T-nutwith threaded shank T-slot nominal size 16 mm | 375315 16 |
| T-nutBlank T-slot nominal size 10 mm | 375320 10 |
| T-nut long T-slot nominal size / thread 14/M12 mm | 375325 14/M12 |
| T-nutBlank T-slot nominal size 12 mm | 375320 12 |
| T-nutwith threaded shank T-slot nominal size 32 mm | 375315 32 |
| T-nutwith threaded shank T-slot nominal size 22 mm | 375315 22 |
| T-nutBlank T-slot nominal size 8 mm | 375320 8 |
| T-nutBlank T-slot nominal size 14 mm | 375320 14 |
| T-nut long T-slot nominal size / thread 20/M18 mm | 375325 20/M18 |
| T-nutBlank T-slot nominal size 6 mm | 375320 6 |
| T-nutwith threaded shank T-slot nominal size 28 mm | 375315 28 |
| T-nutwith threaded shank T-slot nominal size 18 mm | 375315 18 |
| T-nutwith threaded shank T-slot nominal size 36 mm | 375315 36 |
| T-nutwith threaded shank T-slot nominal size 24 mm | 375315 24 |
| T-nutwith threaded shank T-slot nominal size 20 mm | 375315 20 |
| T-nutwith threaded shank T-slot nominal size 12 mm | 375315 12 |
| T-nut long T-slot nominal size / thread 8/M6 mm | 375325 8/M6 |
| T-nut long T-slot nominal size / thread 16/M14 mm | 375325 16/M14 |
| T-nut long T-slot nominal size / thread 28/M24 mm | 375325 28/M24 |
| T-nut long T-slot nominal size / thread 12/M10 mm | 375325 12/M10 |
| T-nut long T-slot nominal size / thread 10/M8 mm | 375325 10/M8 |
| T-nut long T-slot nominal size / thread 22/M20 mm | 375325 22/M20 |

| | |
|--|---------------|
| T-nutBlank T-slot nominal size 20 mm | 375320 20 |
| T-nutwith threaded shank T-slot nominal size 8 mm | 375315 8 |
| T-nutBlank T-slot nominal size 16 mm | 375320 16 |
| T-nutBlank T-slot nominal size 18 mm | 375320 18 |
| T-nutBlank T-slot nominal size 28 mm | 375320 28 |
| T-nut long T-slot nominal size / thread 18/M16 mm | 375325 18/M16 |
| T-nutBlank T-slot nominal size 22 mm | 375320 22 |
| T-nutwith threaded shank T-slot nominal size 6 mm | 375315 6 |
| T-nutwith threaded shank T-slot nominal size 14 mm | 375315 14 |