

TAJIMA

Steel rule, stainless, Length: 1000 mm



Order data

Order number	461620 1000
GTIN	4975364041234
Item class	46R

Description

Version:

Stainless steel, matt surface with sharp contrast graduations.

Upper edge mm graduations, lower 1/2 mm graduations.

Rear with inch/ metric conversion table and table of tapping drill \varnothing .

Material: Stainless steel, INOX

Calibration: F10

Error limit: 0.2 mm

Cross-section width: 35 mm

Cross-section thickness: 1.5 mm

Technical description

Cross-section width	35 mm
Cross-section thickness	1.5 mm
Length	1000 mm
Calibration	F10
Error limit	0.2 mm
Standard	EG I
Graduation on the top edge	1 mm
Graduation on the bottom edge	1/2 mm
Material	Stainless steel, INOX
Type of product	Steel rule

Services

Calibration Steel scale maximum length 1000/2 mm	016100 1000/2
Labelling laser-etched Type	018940