

 Mahr**Internal micrometer set, Measuring range: 6-12mm****Order data**

Order number	428910 6-12
GTIN	4059192010799
Item class	43A

**Description****Version:**

Satin chrome-plated scales and operating parts. Measuring spindle through hardened and ground. Quick drive with integral clutch. Self-centring micrometer head from 12 mm with carbide measuring jaws. From 12 mm **for measuring down to the bottom of the hole**. From 40 mm the micrometer head is of aluminium, to save weight.

**Supplied with:**

Internal micrometers No. 428900 with appropriate setting rings.

**Technical description**

Measuring range	6 - 12 mm
Number of micrometers	3
Number of setting rings	2
Setting ring $\varnothing$	8 / 10 mm
Scale divisions	0.001 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

### Services

CalibrationInternal micrometer set Measuring range 6-12 mm	020550 6-12
--	-------------

### Accessories

Internal micrometer Micromar Measuring range 10-12 mm	428900 10-12
Internal micrometer Micromar Measuring range 8-10 mm	428900 8-10
Setting ringDIN 2250 C Nominal size Ø 7 mm	484030 7
Setting ringDIN 2250 C Nominal size Ø 11 mm	484030 11
Internal micrometer Micromar Measuring range 6-8 mm	428900 6-8
Setting ringDIN 2250 C Nominal size Ø 9 mm	484030 9