

Garant**Steel tape measure "Quickmeter", Band length: 2Hm****Order data**

Order number	461992 2H
GTIN	4045197679512
Item class	41H

Description**Version:**

Stainless steel tape with wear-resistant stove-enamelled markings.
With a handy belt clip. With hinged hook.

Advantage:

The convex camber allows the tape to lie **flat** on the desk, so that dimensions can be read and transferred easily and without errors.

Function:

Runs out automatically at the push of a button and stops when the button is released.

Technical description

Band length	2 m
Tape width	16 mm
Width	24 mm
Ø	62 mm
Standard	EG II
Material	Stainless steel, INOX
Calibration	G1

Type of product

Measuring tape

Services

CalibrationTape measure maximum length 2 m

026240 2