

 Mahr**Internal micrometer set, Measuring range: 12-20mm****Order data**

Order number	428910 12-20
GTIN	4059192010805
Item class	43A

Description**Version:**

Satin chrome-plated scales and operating parts. Measuring spindle through hardened and ground. Quick drive with integral clutch. Self-centring micrometer head from 12 mm with carbide measuring jaws. From 12 mm **for measuring down to the bottom of the hole**. From 40 mm the micrometer head is of aluminium, to save weight.

Supplied with:

Internal micrometers No. 428900 with appropriate setting rings.

Technical description

Number of setting rings	1
Number of micrometers	2
Setting ring \varnothing	16 mm
Measuring range	12 - 20 mm
Scale divisions	0.001 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 12-20 mm	020550 12-20
---	--------------

Accessories

Setting ringDIN 2250 C Nominal size \varnothing 18 mm	484030 18
Internal micrometer Micromar Measuring range 16-20 mm	428900 16-20
Internal micrometer Micromar Measuring range 12-16 mm	428900 12-16
Setting ringDIN 2250 C Nominal size \varnothing 14 mm	484030 14