



Digital internal micrometer with data output, Measuring range: 175-200



Order data

Order number	428930 175-200
GTIN	4059192010881
Item class	43A

Description

Version:

Simple direct reading on the high-contrast display.

Immediately ready for use due to Reference System. Button for changeover between relative and absolute measurement. Screw-on measuring heads can easily be changed.

Self-centring micrometer head, from 12 mm with carbide jaws.

From 40 mm the micrometer head is of aluminium, to save weight.

From 12 mm for measuring down to the bottom of the hole.

Function:

IP52: Protected against splashed water from directions up to 15° (dripping water) and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Extension No. 428950, data cable No. 498940, setting rings No. 484030.

IP Index of Protection: IP 52

Scale divisions: 0.001 mm

Error limit: 0.007 mm

Dimension a: 0.5 mm

Standard measuring depth: 132 mm

Technical description

Measuring range	175 - 200 mm
Standard measuring depth	132 mm

Measuring depth with extension	282 mm
Dimension a	0.5 mm
Error limit	0.007 mm
Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 52
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	Digimatic interface
Interface	USB interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration 3-point inside micrometer maximum measuring range 200 mm	012900 200
Labelling laser-etched Type	018940
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	012910 200
Calibration 3-point inside micrometer maximum measuring range 200 mm	022500 200
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Multi-receiver / USB keyboard interface Type	498975
Setting ring DIN 2250 C Nominal size Ø 190 mm	484030 190
Connecting cable Type USB2	498940 USB2
Extension for internal micrometer Type 25-200	428950 25-200
Connecting cable Type R2	498940 R2
Transmitter Type S4E	498966 S4E
Button cell / special battery Battery type CR2032	081560 CR2032
Connecting cable Type D2	498940 D2
Receiver / USB keyboard interface Type	498965