

 Mahr**Internal micrometer set, Measuring range: 20-50mm****Order data**

Order number	428910 20-50
GTIN	4059192010812
Item class	43A

Description**Version:**

Satin chrome-plated scales and operating parts. Measuring spindle through hardened and ground. Quick drive with integral clutch. Self-centring micrometer head from 12 mm with carbide measuring jaws. From 12 mm **for measuring down to the bottom of the hole**. From 40 mm the micrometer head is of aluminium, to save weight.

Supplied with:

Internal micrometers No. 428900 with appropriate setting rings.

Technical description

Number of micrometers	4
Measuring range	20 - 50 mm
Setting ring \varnothing	25 / 40 mm
Number of setting rings	2
Scale divisions	0.005 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

Calibration Internal micrometer set Measuring range 20-50 mm	020550 20-50
--	--------------

Accessories

Internal micrometer Micromar Measuring range 40-50 mm	428900 40-50
Internal micrometer Micromar Measuring range 20-25 mm	428900 20-25
Setting ring DIN 2250 C Nominal size Ø 45 mm	484030 45
Setting ring DIN 2250 C Nominal size Ø 23 mm	484030 23
Internal micrometer Micromar Measuring range 30-40 mm	428900 30-40
Setting ring DIN 2250 C Nominal size Ø 35 mm	484030 35
Setting ring DIN 2250 C Nominal size Ø 28 mm	484030 28
Internal micrometer Micromar Measuring range 25-30 mm	428900 25-30