

**Internal micrometer, Measuring range: 8-10mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 428990 8-10   |
| GTIN         | 4045197276322 |
| Item class   | 42B           |

**Description****Version:**

Satin chrome plated scales and operating parts (from  $\varnothing$  12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from  $\varnothing$  12 with carbide jaws).

**Supplied with:**

Setting ring (for adjustment) and extension.

**Optional extras:**

Extension No. 428993, setting rings No. 484030.

**Technical description**

|                                |                         |
|--------------------------------|-------------------------|
| Standard measuring depth       | 54 mm                   |
| Measuring range                | 8 - 10 mm               |
| Measuring depth with extension | 154 mm                  |
| Setting ring $\varnothing$     | 8 mm                    |
| Dimension a                    | 1.5 mm                  |
| Error limit                    | 0.004 mm                |
| Scale divisions                | 0.001 mm                |
| Standard                       | Manufacturer's standard |
| Micrometer barrel graduations  | 1/50 mm                 |
| Measurement technology         | analogue                |
| Packaging                      | sturdy box              |

|                 |                             |
|-----------------|-----------------------------|
| Calibration     | B6                          |
| Type of product | 3-point internal micrometer |

### Services

|   |             |
|---|-------------|
| Calibration 3-point internal micrometer maximum measuring range 100R mm       | 022500 100R |
| DAkkS calibration 3-point internal micrometer maximum measuring range 200R mm | 022510 200R |

### Accessories

|  |             |
|--|-------------|
| Setting ring DIN 2250 C Nominal size $\varnothing$ 8 mm  | 484030 8    |
| Setting ring DIN 2250 C Nominal size $\varnothing$ 10 mm | 484030 10   |
| Setting ring DIN 2250 C Nominal size $\varnothing$ 9 mm  | 484030 9    |
| Extension for internal micrometer Type 6-12              | 428993 6-12 |