

 Mahr**Internal micrometer set, Measuring range: 50-100mm****Order data**

Order number	428910 50-100
GTIN	4059192010829
Item class	43A

Description**Version:**

Satin chrome-plated scales and operating parts. Measuring spindle through hardened and ground. Quick drive with integral clutch. Self-centring micrometer head from 12 mm with carbide measuring jaws. From 12 mm **for measuring down to the bottom of the hole**. From 40 mm the micrometer head is of aluminium, to save weight.

Supplied with:

Internal micrometers No. 428900 with appropriate setting rings.

Technical description

Number of setting rings	2
Setting ring \varnothing	60 / 85 mm
Number of micrometers	4
Measuring range	50 - 100 mm
Scale divisions	0.005 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 50-100 mm	020550 50-100
--	---------------

Accessories

Internal micrometer Micromar Measuring range 50-60 mm	428900 50-60
Internal micrometer Micromar Measuring range 70-85 mm	428900 70-85
Internal micrometer Micromar Measuring range 60-70 mm	428900 60-70
Setting ringDIN 2250 C Nominal size Ø 55 mm	484030 55
Internal micrometer Micromar Measuring range 85-100 mm	428900 85-100
Setting ringDIN 2250 C Nominal size Ø 90 mm	484030 90
Setting ringDIN 2250 C Nominal size Ø 80 mm	484030 80
Setting ringDIN 2250 C Nominal size Ø 65 mm	484030 65