

**Tape measure, Band length: 3 m****Order data**

Order number	462010 3
GTIN	4045197207036
Item class	42G

Description**Version:**

Plastic casing with removable belt clip. Automatic tape return and stop, with damping effect. Sliding end hook. Tape measure printed black/red on yellow.

Calibration: G1

Standard: EG II

Tape width: 16 mm

Body length: 66 mm

Body width: 27 mm

Body height: 59 mm

Technical description

Body height	59 mm
Tape width	16 mm
Body length	66 mm
Body width	27 mm
Band length	3 m

Standard	EG II
Calibration	G1
Type of product	Locking tape measure in a frame capsule housing

Services

Calibration Locking tape measure maximum length 5 m	016140 5
Labelling laser-etched Type	018940
5	026250 5
Calibration Tape measure maximum length 5 m	026240 5