



## Internal micrometer, Measuring range: 12-16mm



### Order data

Order number	428990 12-16
GTIN	4045197276346
Item class	42B

### Description

#### Version:

Satin chrome plated scales and operating parts (from  $\varnothing$  12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from  $\varnothing$  12 with carbide jaws).

#### Supplied with:

Setting ring (for adjustment) and extension.

#### Optional extras:

Extension No. 428993, setting rings No. 484030.

### Technical description

Measuring depth with extension	230 mm
Measuring range	12 - 16 mm
Setting ring $\varnothing$	16 mm
Standard measuring depth	80 mm
Dimension a	0.5 mm
Error limit	0.005 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

## Services

Calibration 3-point internal micrometer maximum measuring range 100R mm	022500 100R
DAkkS calibration 3-point internal micrometer maximum measuring range 200R mm	022510 200R

## Accessories

Setting ring DIN 2250 C Nominal size Ø 13 mm	484030 13
Extension for internal micrometer Type 12-20	428993 12-20
Setting ring DIN 2250 C Nominal size Ø 15 mm	484030 15
Setting ring DIN 2250 C Nominal size Ø 16 mm	484030 16
Setting ring DIN 2250 C Nominal size Ø 12 mm	484030 12
Setting ring DIN 2250 C Nominal size Ø 14 mm	484030 14