

**Internal micrometer, Measuring range: 20-25mm****Order data**

Order number	428990 20-25
GTIN	4045197274205
Item class	42B

Description**Version:**

Satin chrome plated scales and operating parts (from \varnothing 12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from \varnothing 12 with carbide jaws).

Supplied with:

Setting ring (for adjustment) and extension.

Optional extras:

Extension No. 428993, setting rings No. 484030.

Technical description

Setting ring \varnothing	25 mm
Measuring range	20 - 25 mm
Dimension a	0.5 mm
Measuring depth with extension	240 mm
Standard measuring depth	90 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration 3-point internal micrometer maximum measuring range 100R mm	022500 100R
DAkkS calibration 3-point internal micrometer maximum measuring range 200R mm	022510 200R

Accessories

Extension for internal micrometer Type 20-30	428993 20-30
Setting ring DIN 2250 C Nominal size Ø 20 mm	484030 20
Setting ring DIN 2250 C Nominal size Ø 25 mm	484030 25
Setting ring DIN 2250 C Nominal size Ø 24 mm	484030 24
Setting ring DIN 2250 C Nominal size Ø 22 mm	484030 22