



## Internal micrometer, Measuring range: 25-30mm



### Order data

Order number	428990 25-30
GTIN	4045197274212
Item class	42B

### Description

#### Version:

Satin chrome plated scales and operating parts (from  $\varnothing$  12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from  $\varnothing$  12 with carbide jaws).

#### Supplied with:

Setting ring (for adjustment) and extension.

#### Optional extras:

Extension No. 428993, setting rings No. 484030.

### Technical description

Dimension a	0.5 mm
Setting ring $\varnothing$	25 mm
Measuring range	25 - 30 mm
Measuring depth with extension	240 mm
Standard measuring depth	90 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

## Services

Calibration 3-point internal micrometer maximum measuring range 100R mm	022500 100R
DAkkS calibration 3-point internal micrometer maximum measuring range 200R mm	022510 200R

## Accessories

Setting ring DIN 2250 C Nominal size Ø 28 mm	484030 28
Setting ring DIN 2250 C Nominal size Ø 26 mm	484030 26
Setting ring DIN 2250 C Nominal size Ø 27 mm	484030 27
Setting ring DIN 2250 C Nominal size Ø 30 mm	484030 30
Setting ring DIN 2250 C Nominal size Ø 25 mm	484030 25
Extension for internal micrometer Type 20-30	428993 20-30