

Mitutoyo
Internal micrometer Holtest, Measuring range: 50-63mm

Order data

Order number	429000 50-63
GTIN	4946368517735
Item class	44A

Description
Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Overall length	156 mm
Measuring depth with extension	255 mm
Measuring range	50 - 63 mm
Standard measuring depth	105 mm
Barrel Ø	23 mm
Dimension a	3.4 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration 3-point internal micrometer maximum measuring range 100 mm	022500 100
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Extension for internal micrometer Type 4/150	429010 4/150
Setting ring DIN 2250 C Nominal size Ø 55 mm	484030 55
Setting ring DIN 2250 C Nominal size Ø 50 mm	484030 50