



Internal micrometer, Measuring range: 75-88mm



Order data

Order number	428990 75-88
GTIN	4045197608024
Item class	42B

Description

Version:

Satin chrome plated scales and operating parts (from \varnothing 12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from \varnothing 12 with carbide jaws). Casing varnished.

Supplied with:

Setting ring (for adjustment) and extension.

Optional extras:

Extension No. 428993, setting rings No. 484030.

Technical description

Setting ring \varnothing	87 mm
Standard measuring depth	117 mm
Measuring range	75 - 88 mm
Measuring depth with extension	267 mm
Dimension a	1 mm
Error limit	0.007 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration3-point internal micrometer maximum measuring range 100R mm	022500 100R
DAkkS calibration3-point internal micrometer maximum measuring range 200R mm	022510 200R

Accessories

Extension for internal micrometer Type 50-100	428993 50-100
Setting ringDIN 2250 C Nominal size \varnothing 80 mm	484030 80