



Internal micrometer, Measuring range: 30-40mm



Order data

| | |
|--------------|---------------|
| Order number | 428990 30-40 |
| GTIN | 4045197274243 |
| Item class | 42B |

Description

Version:

Satin chrome plated scales and operating parts (from \varnothing 12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from \varnothing 12 with carbide jaws).

Supplied with:

Setting ring (for adjustment) and extension.

Optional extras:

Extension No. 428993, setting rings No. 484030.

Technical description

| | |
|--------------------------------|-------------------------|
| Measuring range | 30 - 40 mm |
| Dimension a | 0.5 mm |
| Standard measuring depth | 97 mm |
| Measuring depth with extension | 247 mm |
| Setting ring \varnothing | 40 mm |
| Error limit | 0.006 mm |
| Scale divisions | 0.005 mm |
| Standard | Manufacturer's standard |
| Micrometer barrel graduations | 1/50 mm |
| Measurement technology | analogue |
| Packaging | sturdy box |

| | |
|-----------------|-----------------------------|
| Calibration | B6 |
| Type of product | 3-point internal micrometer |

Services

| | |
|---|-------------|
| Calibration 3-point internal micrometer maximum measuring range 100R mm | 022500 100R |
| DAkkS calibration 3-point internal micrometer maximum measuring range 200R mm | 022510 200R |

Accessories

| | |
|--|--------------|
| Setting ring DIN 2250 C Nominal size Ø 36 mm | 484030 36 |
| Extension for internal micrometer Type 30-50 | 428993 30-50 |
| Setting ring DIN 2250 C Nominal size Ø 35 mm | 484030 35 |
| Setting ring DIN 2250 C Nominal size Ø 40 mm | 484030 40 |
| Setting ring DIN 2250 C Nominal size Ø 34 mm | 484030 34 |
| Setting ring DIN 2250 C Nominal size Ø 30 mm | 484030 30 |
| Setting ring DIN 2250 C Nominal size Ø 38 mm | 484030 38 |