

**Mitutoyo**
**Internal micrometer Holtest, Measuring range: 6-8mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 429000 6-8    |
| GTIN         | 4946368517155 |
| Item class   | 44A           |

**Description**
**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

**Optional extras:**

Extensions No. 429010. Setting rings No. 484030.

**Technical description**

|                                |                         |
|--------------------------------|-------------------------|
| Measuring depth with extension | 157 mm                  |
| Barrel Ø                       | 17 mm                   |
| Standard measuring depth       | 57 mm                   |
| Measuring range                | 6 - 8 mm                |
| Dimension a                    | 2 mm                    |
| Overall length                 | 106 mm                  |
| Error limit                    | 0.004 mm                |
| Scale divisions                | 0.001 mm                |
| Standard                       | Manufacturer's standard |
| Micrometer barrel graduations  | 1/50 mm                 |
| Measurement technology         | analogue                |
| Packaging                      | sturdy box              |
| Calibration                    | B6                      |

|                 |                             |
|-----------------|-----------------------------|
| Type of product | 3-point internal micrometer |
|-----------------|-----------------------------|

## Services

|   |           |
|---|-----------|
| Calibration 3-point internal micrometer maximum measuring range 20 mm | 022500 20 |
|---|-----------|

|  |            |
|--|------------|
| DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm | 022510 200 |
|--|------------|

## Accessories

|   |          |
|---|----------|
| Setting ring DIN 2250 C Nominal size $\varnothing$ 7 mm | 484030 7 |
|---|----------|

|   |          |
|---|----------|
| Setting ring DIN 2250 C Nominal size $\varnothing$ 6 mm | 484030 6 |
|---|----------|

|  |              |
|--|--------------|
| Extension for internal micrometer Type 1/100 | 429010 1/100 |
|--|--------------|

|   |          |
|---|----------|
| Setting ring DIN 2250 C Nominal size $\varnothing$ 8 mm | 484030 8 |
|---|----------|