



Internal micrometer Micromar, Measuring range: 25-30mm



Order data

| | |
|--------------|---------------|
| Order number | 428900 25-30 |
| GTIN | 4059192010638 |
| Item class | 43A |

Description

Version:

Satin chrome-plated scales and operating parts.

Measuring spindle through-hardened and ground.

Quick drive with integral clutch.

Self-centring micrometer head from 12 mm with carbide measuring jaws.

From 12 mm **for measuring down to the bottom of the hole.**

From 40 mm the micrometer head is of aluminium, to save weight.

Optional extras:

Extension No. 428950, Setting rings No. 484030.

Technical description

| | |
|--------------------------------|------------|
| Measuring depth with extension | 218 mm |
| Standard measuring depth | 68 mm |
| Dimension a | 0 mm |
| Measuring range | 25 - 30 mm |
| Error limit | 0.004 mm |
| Scale divisions | 0.005 mm |
| Standard | DIN 863 |
| Micrometer barrel graduations | 1/50 mm |
| Measurement technology | analogue |
| Packaging | sturdy box |

| | |
|-----------------|-----------------------------|
| Calibration | B6 |
| Type of product | 3-point internal micrometer |

Services

| | |
|---|------------|
| Calibration3-point internal micrometer maximum measuring range 50 mm | 022500 50 |
| DAkkS calibration3-point internal micrometer maximum measuring range 200 mm | 022510 200 |

Accessories

| | |
|---|-----------|
| Setting ringDIN 2250 C Nominal size \varnothing 28 mm | 484030 28 |
|---|-----------|