

Mitutoyo**Internal micrometer Holtest, Measuring range: 62-75mm****Order data**

Order number	429000 62-75
GTIN	4946368517742
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Standard measuring depth	105 mm
Barrel Ø	23 mm
Dimension a	3.4 mm
Measuring range	62 - 75 mm
Overall length	156 mm
Measuring depth with extension	255 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration3-point internal micrometer maximum measuring range 100 mm	022500 100
DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Setting ringDIN 2250 C Nominal size Ø 75 mm	484030 75
Setting ringDIN 2250 C Nominal size Ø 65 mm	484030 65
Setting ringDIN 2250 C Nominal size Ø 70 mm	484030 70
Extension for internal micrometer Type 4/150	429010 4/150
Setting ringDIN 2250 C Nominal size Ø 60 mm	484030 60