



## Digital internal micrometer with data output, Measuring range: 125-150mm



### Order data

Order number	428930 125-150
GTIN	4059192010867
Item class	43A

### Description

#### Version:

Simple direct reading on the high-contrast display. Immediately ready for use due to the Reference System. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Button for changeover between relative and absolute measurement. Screw-on measuring heads can easily be changed. Self-centring micrometer head from 12mm with carbide measuring jaws. From 40mm the micrometer head is of aluminium, to save weight. **From 12mm for measuring down to the bottom of the hole.**

#### Function:

IP52: Protected against splashed water from directions up to 15° (dripping water) and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Extension No. 428950, data cable No. 498940, setting rings No. 484030.

### Technical description

Dimension a	0.5 mm
Measuring range	125 - 150 mm
Standard measuring depth	132 mm
Measuring depth with extension	282 mm

Error limit	0.006 mm
Scale divisions	0.001 mm
#Number of batteries contained	1
#Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 52
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	Digimatic interface
Interface	USB interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/428930-125-150>