



Internal micrometer, Measuring range: 40-50mm



Order data

Order number	428990 40-50
GTIN	4045197276353
Item class	42B

Description

Version:

Satin chrome plated scales and operating parts (from \varnothing 12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from \varnothing 12 with carbide jaws).

Supplied with:

Setting ring (for adjustment) and extension.

Optional extras:

Extension No. 428993, setting rings No. 484030.

Technical description

Standard measuring depth	97 mm
Setting ring \varnothing	40 mm
Measuring depth with extension	247 mm
Dimension a	0.5 mm
Measuring range	40 - 50 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration 3-point internal micrometer maximum measuring range 100R mm	022500 100R
DAkkS calibration 3-point internal micrometer maximum measuring range 200R mm	022510 200R

Accessories

Setting ring DIN 2250 C Nominal size Ø 46 mm	484030 46
Extension for internal micrometer Type 30-50	428993 30-50
Extension for internal micrometer Type 50-100	428993 50-100
Setting ring DIN 2250 C Nominal size Ø 44 mm	484030 44
Setting ring DIN 2250 C Nominal size Ø 42 mm	484030 42
Setting ring DIN 2250 C Nominal size Ø 40 mm	484030 40
Setting ring DIN 2250 C Nominal size Ø 50 mm	484030 50
Setting ring DIN 2250 C Nominal size Ø 45 mm	484030 45