



Adaptor jaw fixed, for type: 125



Order data

Order number	361620 125
GTIN	4250364401234
Item class	34A

Description

Version:

Fixed jaw.

Application:

- For fitting existing or self-manufactured jaws.
- For fitting all high pressure jaws No. 362390 to 362600.

Material:

Hardened steel, ground surfaces.

Suitable for:

NC8, Garant-NC, Titan.

Supplied with:

Fastening screws.

Technical description

Height h_1	20 mm
Jaw length l	85 mm
for type	125
suitable for colour code	HiPo
suitable for colour code	Titan

suitable for colour code	Titan2/TitanSense
suitable for colour code	TC
suitable for colour code	LC-GARANT
suitable for colour code	LC
suitable for colour code	LCV125G
suitable for colour code	NC8
suitable for colour code	HOLEX NC
Jaw height h	58 mm
Length l_1	32 mm
Jaw width b	126 mm
Type of product	Vice jaws