

Mitutoyo
Internal micrometer Holtest, Measuring range: 8-10mm

Order data

Order number	429000 8-10
GTIN	4946368517162
Item class	44A

Description
Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Overall length	106 mm
Standard measuring depth	57 mm
Measuring range	8 - 10 mm
Barrel Ø	17 mm
Measuring depth with extension	157 mm
Dimension a	2 mm
Error limit	0.004 mm
Scale divisions	0.001 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6

Type of product	3-point internal micrometer
-----------------	-----------------------------

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
--	------------

Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20
---	-----------

Accessories

Setting ring DIN 2250 C Nominal size \varnothing 10 mm	484030 10
--	-----------

Setting ring DIN 2250 C Nominal size \varnothing 9 mm	484030 9
---	----------

Setting ring DIN 2250 C Nominal size \varnothing 8 mm	484030 8
---	----------

Extension for internal micrometer Type 1/100	429010 1/100
--	--------------