



## Base jaw movable, for type: 125



### Order data

Order number	361500 125
GTIN	4250364401197
Item class	34A

### Description

**Version:**

Movable jaw.

**Application:**

- For fitting all high pressure jaws No. 362390 to 362600.
- For fitting parallel inserts No. 361950; 361960; 361970.

**Material:**

Hardened steel, ground surfaces.

**Suitable for:**

NC8, Garant-NC, Titan.

**Supplied with:**

Fastening screws.

### Technical description

Jaw length l	76 mm
suitable for colour code	HiPo
suitable for colour code	Titan2/TitanSense
suitable for colour code	TC
suitable for colour code	Titan

suitable for colour code	LC
suitable for colour code	LC-GARANT
suitable for colour code	LCV125G
suitable for colour code	NC8
suitable for colour code	HOLEX NC
Jaw height h	39.5 mm
Jaw width b	124.4 mm
for type	125
Type of product	Vice jaws