



## Internal micrometer, Measuring range: 6-8mm



### Order data

Order number	428990 6-8
GTIN	4045197276315
Item class	42B

### Description

#### Version:

Satin chrome plated scales and operating parts (from  $\varnothing$  12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from  $\varnothing$  12 with carbide jaws).

#### Supplied with:

Setting ring (for adjustment) and extension.

#### Optional extras:

Extension No. 428993, setting rings No. 484030.

### Technical description

Measuring depth with extension	154 mm
Standard measuring depth	54 mm
Measuring range	6 - 8 mm
Dimension a	1.5 mm
Setting ring $\varnothing$	6 mm
Error limit	0.004 mm
Scale divisions	0.001 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

### Services

Calibration 3-point internal micrometer maximum measuring range 100R mm	022500 100R
DAkkS calibration 3-point internal micrometer maximum measuring range 200R mm	022510 200R

### Accessories

Setting ring DIN 2250 C Nominal size $\varnothing$ 7 mm	484030 7
Extension for internal micrometer Type 6-12	428993 6-12
Setting ring DIN 2250 C Nominal size $\varnothing$ 6 mm	484030 6
Setting ring DIN 2250 C Nominal size $\varnothing$ 8 mm	484030 8