



Internal micrometer set, Measuring range: 12-20mm



Order data

Order number	428991 12-20
GTIN	4045197276377
Item class	42B

Description

Version:

Satin chrome plated scales and operating parts (from \varnothing 12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from \varnothing 12 with carbide jaws).

Supplied with:

Internal micrometers No. 428990, setting rings (for adjustment) and extension.

Technical description

Setting ring \varnothing	16 mm
Measuring range	12 - 20 mm
Number of setting rings	1
Number of micrometers	2
Error limit	0.005 / 0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	S6
Type of product	3-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 12-20 mm	020550 12-20
---	--------------

Accessories

Setting ringDIN 2250 C Nominal size Ø 14 mm	484030 14
Internal micrometer Measuring range 16-20 mm	428990 16-20
Internal micrometer Measuring range 12-16 mm	428990 12-16
Setting ringDIN 2250 C Nominal size Ø 16 mm	484030 16
Extension for internal micrometer Type 12-20	428993 12-20
Setting ringDIN 2250 C Nominal size Ø 18 mm	484030 18