

Mitutoyo
Internal micrometer Holtest, Measuring range: 87-100mm

Order data

Order number	429000 87-100
GTIN	4946368517766
Item class	44A

Description
Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Measuring range	87 - 100 mm
Dimension a	3.4 mm
Measuring depth with extension	255 mm
Standard measuring depth	105 mm
Barrel Ø	23 mm
Overall length	156 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 100 mm	022500 100

Accessories

Setting ring DIN 2250 C Nominal size \varnothing 100 mm	484030 100
Extension for internal micrometer Type 4/150	429010 4/150
Setting ring DIN 2250 C Nominal size \varnothing 90 mm	484030 90
Setting ring DIN 2250 C Nominal size \varnothing 95 mm	484030 95