

**Mitutoyo****Internal micrometer Holtest, Measuring range: 10-12mm****Order data**

Order number	429000 10-12
GTIN	4946368517179
Item class	44A

**Description****Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

**Optional extras:**

Extensions No. 429010. Setting rings No. 484030.

**Technical description**

Dimension a	2 mm
Standard measuring depth	57 mm
Measuring range	10 - 12 mm
Barrel Ø	17 mm
Measuring depth with extension	157 mm
Overall length	106 mm
Error limit	0.004 mm
Scale divisions	0.001 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

### Services

Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

### Accessories

Setting ring DIN 2250 C Nominal size $\varnothing$ 10 mm	484030 10
Setting ring DIN 2250 C Nominal size $\varnothing$ 12 mm	484030 12
Extension for internal micrometer Type 1/100	429010 1/100
Setting ring DIN 2250 C Nominal size $\varnothing$ 11 mm	484030 11