

**Universal pull-down jaw fixed, for type: 125****Order data**

Order number	361380 125
GTIN	4250364401999
Item class	34A

Description**Application:**

Pull-down with ground spring leaves for rough and machined surfaces. Click quick-change system for mounting click inserts. High clamping accuracy for parallel or precision angle machining.

Clamping faces leave virtually no visible impression.

Supplied with:

Spring leaves.

Jaw width b: 124.4 mm

c: 24 mm

c₁: 34 mm

Jaw height h: 39.5 mm

Height h₁: 20 mm

Jaw length l: 92 mm

Technical description

c	24 mm
for type	125
Jaw height h	39.5 mm
suitable for colour code	Titan
suitable for colour code	Titan 2

suitable for colour code	HiPo
suitable for colour code	TC
suitable for colour code	LC
suitable for colour code	LC-Garant
suitable for colour code	LCV125G
suitable for colour code	NC8
Length l_1	43 mm
c_1	34 mm
Jaw length l	92 mm
Jaw width b	124.4 mm
Height h_1	20 mm
Length l_2	8.8 mm
Type of product	Vice - jaw