



## Internal micrometer, Measuring range: 62-75mm



### Order data

Order number	428990 62-75
GTIN	4045197608017
Item class	42B

### Description

#### Version:

Satin chrome plated scales and operating parts (from  $\varnothing$  12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from  $\varnothing$  12 with carbide jaws). Casing varnished.

#### Supplied with:

Setting ring (for adjustment) and extension.

#### Optional extras:

Extension No. 428993, setting rings No. 484030.

### Technical description

Measuring depth with extension	267 mm
Standard measuring depth	117 mm
Dimension a	1 mm
Setting ring $\varnothing$	62 mm
Measuring range	62 - 75 mm
Error limit	0.007 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

### Services

Calibration3-point internal micrometer maximum measuring range 100R mm	022500 100R
DAkkS calibration3-point internal micrometer maximum measuring range 200R mm	022510 200R

### Accessories

Extension for internal micrometer Type 50-100	428993 50-100
Setting ringDIN 2250 C Nominal size Ø 70 mm	484030 70