



Internal micrometer set, Measuring range: 20-50mm



Order data

Order number	428991 20-50
GTIN	4045197276384
Item class	42B

Description

Version:

Satin chrome plated scales and operating parts (from \varnothing 12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from \varnothing 12 with carbide jaws).

Supplied with:

Internal micrometers No. 428990, setting rings (for adjustment) and extension.

Technical description

Number of setting rings	2
Setting ring \varnothing	25 / 40 mm
Number of micrometers	4
Measuring range	20 - 50 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

Calibration Internal micrometer set Measuring range 20-50 mm	020550 20-50
--	--------------

Accessories

Setting ring DIN 2250 C Nominal size Ø 45 mm	484030 45
Internal micrometer Measuring range 30-40 mm	428990 30-40
Setting ring DIN 2250 C Nominal size Ø 35 mm	484030 35
Setting ring DIN 2250 C Nominal size Ø 25 mm	484030 25
Internal micrometer Measuring range 20-25 mm	428990 20-25
Setting ring DIN 2250 C Nominal size Ø 40 mm	484030 40
Internal micrometer Measuring range 40-50 mm	428990 40-50
Internal micrometer Measuring range 25-30 mm	428990 25-30
Extension for internal micrometer Type 20-30	428993 20-30
Setting ring DIN 2250 C Nominal size Ø 27 mm	484030 27
Setting ring DIN 2250 C Nominal size Ø 22 mm	484030 22