

Mitutoyo
Internal micrometer Holtest, Measuring range: 12-16mm

Order data

Order number	429000 12-16
GTIN	4946368517674
Item class	44A

Description
Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Barrel Ø	23 mm
Overall length	127 mm
Measuring depth with extension	230 mm
Measuring range	12 - 16 mm
Dimension a	2.6 mm
Standard measuring depth	80 mm
Error limit	0.004 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6

Type of product	3-point internal micrometer
-----------------	-----------------------------

Services

Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20
---	-----------

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
--	------------

Accessories

Setting ring DIN 2250 C Nominal size \varnothing 15 mm	484030 15
--	-----------

Extension for internal micrometer Type 2/150	429010 2/150
--	--------------

Setting ring DIN 2250 C Nominal size \varnothing 14 mm	484030 14
--	-----------

Setting ring DIN 2250 C Nominal size \varnothing 16 mm	484030 16
--	-----------

Setting ring DIN 2250 C Nominal size \varnothing 13 mm	484030 13
--	-----------

Setting ring DIN 2250 C Nominal size \varnothing 12 mm	484030 12
--	-----------