

**Stepped jaw fixed, for type: 125****Order data**

Order number	361420 125
GTIN	4250364401111
Item class	34A

**Description****Version:**

Fixed jaw.

Sizes 90, 125, and 160 with **Click quick-change system**, for No. 361440 only in sizes 90 and 125.  
Tapped hole for high pressure jaws in sizes 125 and 160.

**Application:**

For clamping parallel pre-machined components. Tapped holes M10 and M6 for taking front jaws with click quick-change system for click inserts and jaws.

Accepts parallel inserts on high side or stepped side (No. 361950; 361960; 361970).

**Material:**

Hardened steel, ground surfaces.

**Suitable for:**

All types TC, LC, Garant-NC, Titan and the earlier NC version.

**Supplied with:**

Fastening screws. 1 stepped jaw.

**Technical description**

Length $l_1$	43 mm
Jaw height $h$	39.5 mm
Height $h_1$	20 mm

suitable for colour code	HiPo
suitable for colour code	Titan
suitable for colour code	Titan2/TitanSense
suitable for colour code	TC
suitable for colour code	LC
suitable for colour code	LC-GARANT
suitable for colour code	LCV125G
suitable for colour code	NC8
suitable for colour code	HOLEX NC
for type	125
Jaw width b	124.4 mm
Jaw length l	92 mm
Type of product	Vice jaws