

**Mitutoyo****Internal micrometer Holtest, Measuring range: 16-20mm****Order data**

Order number	429000 16-20
GTIN	4946368517681
Item class	44A

**Description****Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

**Optional extras:**

Extensions No. 429010. Setting rings No. 484030.

**Technical description**

Barrel Ø	23 mm
Standard measuring depth	80 mm
Dimension a	2.6 mm
Measuring depth with extension	230 mm
Overall length	127 mm
Measuring range	16 - 20 mm
Error limit	0.004 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

## Services

Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

## Accessories

Setting ring DIN 2250 C Nominal size Ø 19 mm	484030 19
Setting ring DIN 2250 C Nominal size Ø 20 mm	484030 20
Setting ring DIN 2250 C Nominal size Ø 17 mm	484030 17
Setting ring DIN 2250 C Nominal size Ø 16 mm	484030 16
Setting ring DIN 2250 C Nominal size Ø 18 mm	484030 18
Extension for internal micrometer Type 2/150	429010 2/150