

Mitutoyo**Internal micrometer Holtest, Measuring range: 125-150mm****Order data**

Order number	429000 125-150
GTIN	4946368517780
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Measuring depth with extension	297 mm
Dimension a	19.6 mm
Measuring range	125 - 150 mm
Barrel Ø	23 mm
Standard measuring depth	147 mm
Overall length	249 mm
Error limit	0.01 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration3-point internal micrometer maximum measuring range 200 mm	022500 200
DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Setting ringDIN 2250 C Nominal size Ø 125 mm	484030 125
Setting ringDIN 2250 C Nominal size Ø 140 mm	484030 140
Extension for internal micrometer Type 4/150	429010 4/150