

Mitutoyo**Internal micrometer Holtest, Measuring range: 20-25mm****Order data**

Order number	429000 20-25
GTIN	4946368517698
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Measuring depth with extension	240 mm
Barrel Ø	23 mm
Dimension a	2.6 mm
Measuring range	20 - 25 mm
Overall length	140 mm
Standard measuring depth	90 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50

Accessories

Setting ring DIN 2250 C Nominal size Ø 25 mm	484030 25
Setting ring DIN 2250 C Nominal size Ø 20 mm	484030 20
Setting ring DIN 2250 C Nominal size Ø 24 mm	484030 24
Extension for internal micrometer Type 3/150	429010 3/150
Setting ring DIN 2250 C Nominal size Ø 22 mm	484030 22