

**Mitutoyo****Internal micrometer Holtest, Measuring range: 25-30mm****Order data**

Order number	429000 25-30
GTIN	4946368517704
Item class	44A

**Description****Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

**Optional extras:**

Extensions No. 429010. Setting rings No. 484030.

**Technical description**

Dimension a	2.6 mm
Measuring depth with extension	240 mm
Standard measuring depth	90 mm
Barrel Ø	23 mm
Overall length	140 mm
Measuring range	25 - 30 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

## Services

Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

## Accessories

Setting ring DIN 2250 C Nominal size Ø 25 mm	484030 25
Setting ring DIN 2250 C Nominal size Ø 30 mm	484030 30
Setting ring DIN 2250 C Nominal size Ø 27 mm	484030 27
Extension for internal micrometer Type 3/150	429010 3/150
Setting ring DIN 2250 C Nominal size Ø 28 mm	484030 28
Setting ring DIN 2250 C Nominal size Ø 26 mm	484030 26