

Mitutoyo
Internal micrometer Holtest, Measuring range: 30-40mm

Order data

Order number	429000 30-40
GTIN	4946368517711
Item class	44A

Description
Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Measuring depth with extension	248 mm
Barrel Ø	23 mm
Dimension a	3.4 mm
Standard measuring depth	98 mm
Overall length	140 mm
Measuring range	30 - 40 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50

Accessories

Setting ring DIN 2250 C Nominal size Ø 38 mm	484030 38
Setting ring DIN 2250 C Nominal size Ø 30 mm	484030 30
Setting ring DIN 2250 C Nominal size Ø 35 mm	484030 35
Setting ring DIN 2250 C Nominal size Ø 36 mm	484030 36
Extension for internal micrometer Type 3/150	429010 3/150
Setting ring DIN 2250 C Nominal size Ø 34 mm	484030 34
Setting ring DIN 2250 C Nominal size Ø 40 mm	484030 40
Setting ring DIN 2250 C Nominal size Ø 32 mm	484030 32