



## Adaptor jaw movable, for type: 125



### Order data

Order number	361600 125
GTIN	4250364400879
Item class	34A

### Description

**Version:**

Movable jaw.

**Application:**

- For fitting existing or self-manufactured jaws.
- For fitting all high pressure jaws No. 362390 to 362600.

**Material:**

Hardened steel, ground surfaces.

**Suitable for:**

NC8, Garant-NC, Titan.

**Supplied with:**

Fastening screws.

### Technical description

Jaw length l	80 mm
Length l <sub>1</sub>	32 mm
Jaw height h	58 mm
Height h <sub>1</sub>	20 mm
suitable for colour code	HiPo

suitable for colour code	Titan
suitable for colour code	Titan2/TitanSense
suitable for colour code	Duo Plus
suitable for colour code	TC
suitable for colour code	LC
suitable for colour code	LC-GARANT
suitable for colour code	LCV125G
suitable for colour code	NC8
suitable for colour code	HOLEX NC
for type	125
Jaw width b	126 mm
Type of product	Vice jaws