



Stepped jaw movable, for type: 90



Order data

Order number	361400 90
GTIN	4250364401029
Item class	34A

Description

Version:

Movable jaw.

Sizes 90, 125, and 160 with **Click quick-change system**, for No. 361440 only in sizes 90 and 125.

Application:

For clamping parallel pre-machined components. Tapped holes M10 and M6 for taking front jaws with click quick-change system for click inserts and jaws.

Accepts parallel inserts on high side or stepped side (No. 361950; 361960; 361970).

Material:

Hardened steel, ground surfaces.

Suitable for:

All types TC, LC, Garant-NC, Titan and the earlier NC version.

Supplied with:

Fastening screws. 1 stepped jaw.

Technical description

Jaw width b	89.5 mm
Length l ₁	31 mm
Jaw height h	34 mm

Height h ₁	16 mm
Jaw length l	56 mm
suitable for colour code	Duo
suitable for colour code	TC
suitable for colour code	LC
suitable for colour code	NC8
for type	90
Type of product	Vice jaws