

**Stepped jaw movable, for type: 125****Order data**

Order number	361400 125
GTIN	4250364401036
Item class	34A

Description**Version:**

Movable jaw.

Sizes 90, 125, and 160 with **Click quick-change system**, for No. 361440 only in sizes 90 and 125.

Application:

For clamping parallel pre-machined components. Tapped holes M10 and M6 for taking front jaws with click quick-change system for click inserts and jaws.

Accepts parallel inserts on high side or stepped side (No. 361950; 361960; 361970).

Material:

Hardened steel, ground surfaces.

Suitable for:

All types TC, LC, Garant-NC, Titan and the earlier NC version.

Supplied with:

Fastening screws. 1 stepped jaw.

Technical description

Jaw length l	70 mm
Jaw width b	124.4 mm
Height h ₁	20 mm

suitable for colour code	Titan
suitable for colour code	Titan2/TitanSense
suitable for colour code	HiPo
suitable for colour code	Duo Plus
suitable for colour code	TC
suitable for colour code	LC-GARANT
suitable for colour code	LC
suitable for colour code	LCV125G
suitable for colour code	NC8
suitable for colour code	HOLEX NC
Jaw height h	39.5 mm
for type	125
Length l ₁	40 mm
Type of product	Vice jaws