



## Pole extensions for the MillTec Basic electro-permanent magnetic clamping plate, Type: PFR



### Order data

Order number	383510 PFR
GTIN	2050001782830
Item class	38D

### Description

#### Advantage:

- Quick and reliable clamping of uneven parts.
- Even clamping force over the entire face, without distorting the workpiece.
- Clamping of distorted fabrications in a very short time.
- Holes can be bored through the entire workpiece without damaging the magnetic plate.
- 20 % better magnetic power than conventional pole extensions.
- Integral threaded stud permits quick and easy positioning.
- Encapsulated design prevents ingress of chips.

#### Suitable for :

No. 383050

Ø: 70 mm

Height: 45 mm

Version: fixed

### Technical description

Ø	70 mm
---	-------

Version	fixed
Height	45 mm
Type of product	Extension