

TAJIMA

Tape measure, non-slip casing extra sturdy, Band length: 7 m



Order data

Order number	462330 7
GTIN	4975364029140
Item class	46R

Description

Version:

- **Tape with particularly high buckling stability.**
- **Totally shock-proof plastic housing with removable belt clip.**
- **Automatic tape return and stop.**
- **Shock absorber reduces load during tape return.**
- **Sliding end hook.**
- **Tape measure printed black/red on yellow, acrylic coated for high abrasion resistance**
- **Long-lasting spring of high grade steel.**
- **Additionally with rubberised casing.**
- **Tape printed both sides.**

Calibration: G1

Standard: EG II

Tape width: 25 mm

Body length: 77 mm

Body width: 34 mm

Body height: 73 mm

Technical description

Tape width	25 mm
Body height	73 mm
Body length	77 mm

Body width	34 mm
Band length	7 m
Standard	EG II
Calibration	G1
Type of product	Locking tape measure in a frame capsule housing

Services

Calibration Locking tape measure maximum length 10/2 m	016140 10/2
Labelling laser-etched Type	018940
Calibration Tape measure maximum length 10/2 m	026240 10/2
30/2	026250 30/2