

Tajima**Tape measure, non-slip casing extra sturdy, Band length: 10m****Order data**

Order number	462330 10
GTIN	4975364029157
Item class	46R

Description**Version:**

- **Tape measure with particularly high buckling stability.**
- **Totally shock-proof plastic housing with removable belt clip.**
- **Automatic tape return and stop.**
- **Shock absorber reduces the impact at tape return.**
- **Sliding end hook.**
- **Tape measure printed black/red on yellow, acrylic coated for high abrasion resistance.**
- **Long-lasting spring made of high grade steel.**
- **Additionally with rubberised casing.**
- **Tape printed both sides.**

Technical description

Body height	98 mm
Tape width	25 mm
Body length	95 mm
Body width	45 mm
Band length	10 m
Standard	EG II
Calibration	G1

Type of product

Measuring tape

Services

CalibrationTape measure maximum length 10/2 m

026240 10/2